

S600

Portable Compressed Air Purity Analyzer





ISO 8573-1 ALL IN ONE Particle concentration, Dew Point, Oil vapor



HIGH PRECISION Accurate measurements





MEASUREMENT

GUIDED



PORTABLE MULTI-TOOL Can be carried with one hand



PDF REPORTING Create ISO 8573-1 reports on the device



Benefits

- All-in-one device measures Particle concentration, dew point and oil vapor
- Measures additionally the temperature and pressure
- Software guided measurement makes it easy to generate reliable results
- Report generator creates PDFs for ISO 8573-1 audits
- Ultra portable and compact design

Plug & Play Measurement — Save Precious Time

ISO 8573 compliant purity quantifications of compressed air systems are bound to time-consuming installations and long-lasting test runs ... It's time for a revolution: The S600 is unlike its competition.

It combines the latest sensor technology, softwareguided measurements and a time-saving setup into a handy, touchscreen controlled multi-tool. With our S600 you will finish measurement runs in much less time than with your traditional method, after that you don't ever want to leave your new comfort zone again. Trust us.

Remote connection

By connecting a LTE/4G modem to the designated USB port, S600 can be monitored remotely through S4A software.

Monitoring of All Relevant Contaminants



Particle Concentration Measurement $0.1 < d \le 0.5 \ \mu m \ / \ 0.5 < d \le 1.0 \ \mu m \ / \ 1.0 < d \le 5.0 \ \mu m \ / \ 5.0 \ \mu m < d$



Dew Point Measurement -100 ... +20 °C Td



Oil Vapor Measurement 0.001... 5.000 mg/m³

ISO 8573-1 Classification



S600 Compressed Air Purity Analyzer

5 in 1 Measuring Device

The S600 is the portable multi-tool for ISO 8573-1 compressed air purity measurements. It measures, records and validates quality parameters like particle concentration, dew point, oil vapor contents, temperature and the pressure of compressed air systems.



Particle Concentration Measurement

- Measurement methods according to ISO 8573-4
 standards (together with isokinetic sampling device)
- Latest laser detection technology
- Smallest particle size 30 ... 70 %, next bigger sizes 90 ... 110 % per ISO 21501-4



Dew Point Measurement

- Large ranges due to the unique multiple sensor technology
- Long-term stable and well-proven measurement methods
- High precision with an accuracy of ± 2 °C Td



Oil Vapor Measurement

- Latest photoionisation detector (PID) with self-calibration
- Measuring range according to ISO 8573-1 Class 1 to Class 5
- High precision with 5 % of reading \pm 0.003 mg/m³ accuracy



Pressure Measurement

- State of the art sensor technology
- Additional quality data about the compressed air system



Integrated Data Logger

- Integrated data logger records all channels in parallel for later analysis
- 5" touchscreen allows you to interact with the device on site. There is no need for a PC to manage the device.

ISO 8573-4 Isokinetic Sampling Device



Applications

Air quality measurements in medical, pharmaceutical, food and beverage applications
 Compressed air quality audits in regards to the ISO 8573-1
 Point-of-use measurements to ensure process safety and quality in all applications
 Monitoring of high tech applications with strict air

purity requirements

Create Compressed Air Quality Reports

The S600 enables users to create powerful PDF reports directly on site. The reports are following the recommendations stated in the ISO 8573, additionally customer related data as well as service provider details can be entered on-screen, making it even easier to perform audits and to create meaningful reports.

PDF reports can be created from any recordings on the device and are copied on the fly to a connected USB drive for direct print-outs.

Massurament davica				しつい	- 1
Model:	5800			Resmart Measure it	- 1
Manufacturer:	SUTO ITEC				- 1
Last calibration: 14	22. June 2022				- 1
Serial number:	1234 5678				- 1
Location Information			Service provider		- 1
Customer:	Customer GmbH		Company:	SUTO ITEC GmbH	
feater name:	Max Mustermann		Phone:	0049 7634 504 88 00	
Weasurement Location:	Prod. Line 1		Email:	info@suto-itec.com	
Measurement Point:	Machine 1				
Target classes ISO 851	3-1 (weiselied ky user)		Measurement information		
Particles:	2		Measurement started.	14:56:00 22. August 2021	
Humidity:	3		Measurement stopped:	15:26:00 22. August 2021	
Dil:	2		Measurement duration:	00:30:00	
Measurement resul	ts				
System / Measuremen	conditions				
Wedium Temperature (*1	31.0		Gas Type:	Air	- 1
Medium Pressure (bar)	5.62		Particle counter flow rate:	2.83 limin */- 0.05 limin	
Declared Particle conc	entration in cn/m3 (d	Particle size	[referring to 20°C; 100 kPa]		- 1
Davel	Last salue	Measured value	Estation	IEO 8573-1 Case measured	- 1
0.1 µm ≺ d ≤ 0.5 µm	s 400000	200000	passed		
0.5 µm ≺ d ≤ 1.0 µm	s 6000	5000	passed	2	2
1.0 µm < d ≤ 5.0 µm	s 100	60	passed		- 1
i > 5.0 μm	\$0	0	passed		- 1
Declared Pressure dev	v point in *C (referring	to actual and n	eference conditions 20 °C; 7 ba	nigi) "	- 1
Selection conditions	Land value	Measured value	Estudios	IIO 8573 1 Case researed	- 1
actual conditions	N.S.*	-24.6	N.S.*	3	- 1
20°C / 7 ber(g)	\$ -20.0	-22.7	pessed		- 1
Declared content of Oi	l vapour in mg/m³ (ref	erring to 20°C;	100 kPa]		- 1
Reference conditions	Linit value	Measured value	Endudion	IIIO 8573-1 Case measured	
20 °C / 100 kPa	\$0.1	0.008	passed	1	- 1
Measurement equipme	int				
Particle concentration:	Laser optical particle	counter Anne	ny 10% @ 0.1 < 4 < 0.15 µm; 10% @ 4 > 0	15pm Range 0.1<44.80pm+4>80pm	
Pressure dew point:	Polymer + QCM sens	Of Asses	wy +0.2 %	Range: 100	
Oil vapour:	PID Sensor	Anna	wy <0% of measured value <0.020 mp/m	Range 0.001 8.000 regim ¹	- 1
Approval					- 1
Signature Tester:	Sian	ature Custome	cPia	ice / Date:	
Notes / Cumments					
					- 1
 Pur further details, please sheck 1 8. Assorbing to 100: 8173-3 the satio lated in the leaf resol. 	he calification certificate. alled pressure dew point at 2010 o	end 7 berigt must be o	sed for an IBO 8173-1 classification, still the pr	essure dev port at actual conditions shall be	
and the second					
manufactor and other objects					

ISO 8573-1 Compressed Air Classes

ISO 8573-1:2010 is the main publication of the ISO 8573 series of standards, because it contains the permissible amount of contaminants per cubic meter of compressed air is fixed.

	Particle Concentration			Pressure Dew Point	Oil Concentration	
Class	cn/m³		26 (25)			
	$0.1 < d \le 0.5 \ \mu m$	$0.5 < d \le 1.0 \ \mu m$	$1.0 < d \le 5.0 \ \mu m$	°C (°F)	mg/m²	
0		As specified by	the equipment use	er or supplier and more stringent	than class 1	
1	≤ 20,000	≤ 400	≤ 10	≤ -70 (94.0)	≤ 0.01	
2	≤ 400,000	≤ 6,000	≤ 100	≤ -40 (-40.0)	≤ 0.1	
3	not specified	≤ 90,000	≤ 1,000	≤ -20 (-4.0)	≤ 1	
4	not specified	not specified	≤ 10,000	≤ +3 (+37.4)	≤ 5	
5	not specified	not specified	≤ 100,000	≤ +7 (+45.6)	> 5	
6	×	х	×	≤ +10 (+50.0)	X	

Why should you focus on your ISO 8573-1 specifications?

Certain industries like the pharmaceutical and food industry requires high-quality compressed air. By meeting the ISO 8573-1 standard requirements you can:

Ensure Process and Product Safety:

Potential incidents, like contaminants meeting food via water and oil, can create safety concerns and unreliable processes.

Avoid Production Failures and Poor Quality Finishes:

Contaminants mixing with applications effect product results.

Prevent production downtime:

Processes and machines are stopped to find and eliminate the contamination issues.

Dimensions



Measurement

Particle concentration	
Accuracy	Counting Efficiency according ISO 21501-4
	30 70 % of d > 0.1 μm
	90 110 % of d \geq 0.3 μm
Selectable units	cn/m ³ , cn/ft ³
Measuring range	$0.1 < d \le 0.5 \ \mu m$
	$0.5 < d \le 1.0 \ \mu m$
	1.0 < d ≤ 5.0 μm
	5.0 μm < d
Sensor	Laser optical particle counter
Sampling rate	1 min.
Flow rate	2.83 l/min
Pressure Dew Point	
Accuracy	± 1 °C Td (0 20 °C Td)
	± 2 °C Td (-70 0 °C Td)
	± 3 °C (-10070 °C Td)
Selectable units	°C, °F
Measuring range	-100 +20 °C Td
Sensor	QCM + Polymer
Response time (t90)	-20 °C Td -> -60 °C Td = < 240 sec
	-60 °C Td -> -20 °C Td = < 30 sec @ 4 l/min
Oil vapor	
Accuracy	5 % of value +/- 0.003 mg/m ³
Detection limit	0.001 mg/m ³
Resolution	0.001 mg/m ³
Selectable units	mg/m ³
Measuring range	0.001 5.000 mg/m ³
Sensor	PID (Photoionisation detector)
UV lamp lifetime	1 year or 6000 working hours, whichever comes first
Sampling rate	1 sec.
Pressure	
Accuracy	0.5 % FS
Measuring range	0.1 1.6 MPa(g)
Sensor	Piezo resistive sensor
Temperature	
Accuracy	± 0.3 °C
Measuring range	-30 +70 °C
Sensor	Pt100
Reference conditions	
Selectable conditions	ISO1217 20 °C 1000 mbar

Signal / Interface & Supply

Fieldbus	
Protocol	Modbus/TCP
Update rate	1 / sec.
Power Supply	
Voltage supply	Mains supply adapter (AC/DC) Input: 100 240 VAC, 50/60 Hz, 1.4 A
	Output: 24 VDC, 2.5 A, 60 W max.
Current consumption	1.4 A
Interface	
USB	USB Micro with OTG support
LTE/4G USB	USB Port for 4G/LTE Modem

General data	
Configuration	
Others	Device comes pre-configured Configuration can be done via on-screen touch
Display	
Integrated	Touchscreen, Size: 5", Resolution: 800 x 480 px
Data Logger	
Storage	Up to 3 million recorded data sets (10 channels each)
Report	Integrated report generator for PDF export
Material	
Process connection	Brass nickel-plated, FKM
Housing	PC + ABS, Al alloy
Miscellaneous	
Electrical connection	2-Pin, push-pull socket
Protection class	IP54 (cover lid closed)
Approvals	CE
Process connection	Micro quick connector, full passthrough, male (1.5 m hose with coupling included)
Weight	9.8 kg
Operating conditions	
Medium	Compressed Air, Nitrogen N ₂ , Carbon dioxide CO ₂ (software setting)
Medium quality	ISO 8573-1: 4.4.4 or better
Medium temperature	0 + 40 °C
Medium humidity	Medium humidity < 40 % rH, no condensation
Operating pressure	0.3 1.5 MPa(g)
Ambient temperature	0 +50 °C
Ambient humidity	0 90 % rH
Storage temperature	-10 + 70 °C
Transport temperature	-10 + 70 °C

Isokinetic Sampling Device

Measurement		
Isokinotis Samplin	ng Davisa	
isokinetic sampling Device		
Measuring unit	Measuring unit Sampling pipe with integrated isokinetic sampling tube, flow regulation and control by integrated flow sensor, to be used for particle measure- ments according to ISO 8573-4	
Flow meter unit	Thermal mass flow meter (only for isoki- netic flow setup, no system flow measu- rement)	
Sensor	Thermal mass flow sensor	
Accuracy	3 % o. RDG	

Signal Interface & Supply

Connection	Communication to S600 (cable included)
Update rate	1 / sec.

General data	
Material	
Process connection	Brass nickel-plated, FKM
Housing	PC + ABS, Al alloy
Main unit	Al alloy
Isokinetic tube	Stainless steel1.4404 (SUS 316L)
Miscellaneous	
Electrical connection	M8
Protection class	IP54
	IEC 61326-1
Process connection	Micro quick connector, full passth- rough, male (1.5 m hose with coupling included)
Operating conditions	
Medium	Compressed Air, Nitrogen N ₂ , Carbon dioxide CO ₂ (software setting)
Medium quality	ISO 8573-1: 4.4.4 or better
Medium temperature	0 + 40 °C
Medium humidity	Medium humidity < 40 % rH, no condensation
Operating pressure	0.3 1.5 MPa(g)
Ambient temperature	0 +50 °C
Ambient humidity	0 90 % rH
Storage temperature	-10 + 70 °C
Transport temperature	-10 + 70 °C

Dimensions Isokinetic Sampling Device







Please use the following tables to assist in placing your order with our sales staff.

S600 Portable Compressed Air Purity Analyzer (Portable Version)

Order No.	Description
P560 0600	Touch screen interface, data logger, guided measurement, PDF report generator, USB port and Ethernet port with Modbus/TCP Particle d: $0.1 < d <= 0.5$, μ m $0.5 < d <= 1.0 \mu$ m, $1.0 < d <= 5.0 \mu$ m, $d > 5.0 \mu$ m Dew point: -100 +20 °C Td Oil vapor: 0.001 5.000 mg/m ³
	Including: • Portable Compressed Air Purity Analyzer in a hand carry case with handle and shoulder belt • USB OTG memory stick • Purge filter for pre-measurement (test kit) • Power supply, 230 VAC / 24 VDC 50/60 Hz • 2 x Connection hose 1.5 m, one end quick coupling, one end compressed air coupling • Certificate of calibration • Operation and instruction manual
A1670	USB 4G dongle for S551/S600, including S4A software

Isokinetic Sampling Device

Order No. Description

A554 0600

Isokinetic sampling device for particle measurement according to ISO 8573

Including:

- Isokinetic sampling pipe
- Flow sensor mounted on pipe
- Certificate of calibration
- Connection cable to \$600
- Connection hose 150 mm, both ends quick coupling
- Connection hose 700 mm, both ends quick coupling
- Connection hose 1.5 m, one end quick coupling, one end compressed air coupling
- Transport case to carry the device, hoses and cables



www.suto-itec.com